



Novus® Distribution Panel

The West-Call® Novus® Distribution Panel is the audio controller for up to eight masters and 16 audio paths. The Distribution Panels are configurable with the homerun modules on the back plane to handle 16 through 128 IDs. IP protocol is used for communication between the audio controllers, homerun controllers, and the master computers.

Features

- ▶ 16 Audio Paths
- ▶ Connect up to Eight Master Stations
- ▶ 128 ID Points per Central
- ▶ Eight Auxiliary Audio Inputs
- ▶ Uses IPX Protocol
- ▶ Diagnostic Display
- ▶ Voltage Test Points
- ▶ Capable of Networking Up to Eight Centrals

Ordering Information

DESCRIPTION	MODEL NO.
West-Call® Novus® Distribution Panel with 4x8 Audio Switch Matrix on 36x24 back panel. No Field Home Run (FHR) Modules. Distribution Panel requires a TC-3624/6 (30116001) Terminal Cabinet.	NOVUS/3624/00
West-Call® Novus® Distribution Panel with 4x8 Audio Switch Matrix on 36x24 back panel. 1 Field Home Run (FHR) Module. Each Field Home Run Module supports up to 16 patient rooms. A 28V power supply is required for each FHR. Distribution Panel requires a TC-3624/6 (30116001) Terminal Cabinet.	NOVUS/3624/01
West-Call® Novus® Distribution Panel with 4x8 Audio Switch Matrix on 36x24 back panel. 2 Field Home Run (FHR) Modules. Each Field Home Run Module supports up to 16 patient rooms. A 28V power supply is required for each FHR. Distribution Panel requires a TC-3624/6 (30116001) Terminal Cabinet.	NOVUS/3624/02
West-Call® Novus® Distribution Panel with 4x8 Audio Switch Matrix on 36x24 back panel. 3 Field Home Run (FHR) Modules. Each Field Home Run Module supports up to 16 patient rooms. A 28V power supply is required for each FHR. Distribution Panel requires a TC-3624/6 (30116001) Terminal Cabinet.	NOVUS/3624/03
West-Call® Novus® Distribution Panel with 4x8 Audio Switch Matrix on 36x24 back panel. 4 Field Home Run (FHR) Modules. Each Field Home Run Module supports up to 16 patient rooms. A 28V power supply is required for each FHR. Distribution Panel requires a TC-3624/6 (30116001) Terminal Cabinet.	NOVUS/3624/04
West-Call® Novus® Distribution Panel with 4x8 Audio Switch Matrix on 36x24 back panel. 5 Field Home Run (FHR) Modules. Each Field Home Run Module supports up to 16 patient rooms. A 28V power supply is required for each FHR. Distribution Panel requires a TC-3624/6 (30116001) Terminal Cabinet.	NOVUS/3624/05
West-Call® Novus® Distribution Panel with 4x8 Audio Switch Matrix on 36x24 back panel. 6 Field Home Run (FHR) Modules. Each Field Home Run Module supports up to 16 patient rooms. A 28V power supply is required for each FHR. Distribution Panel requires a TC-3624/6 (30116001) Terminal Cabinet.	NOVUS/3624/06
West-Call® Novus® Distribution Panel with 4x8 Audio Switch Matrix on 36x24 back panel. 2 Field Home Run (FHR) Modules. Each Field Home Run Module supports up to 16 patient rooms. A 28V power supply is required for each FHR. Distribution Panel requires a TC-3624/6 (30116001) Terminal Cabinet.	NOVUS/3624/07
West-Call® Novus® Distribution Panel with 4x8 Audio Switch Matrix on 36x24 back panel. 2 Field Home Run (FHR) Modules. Each Field Home Run Module supports up to 16 patient rooms. A 28V power supply is required for each FHR. Distribution Panel requires a TC-3624/6 (30116001) Terminal Cabinet.	NOVUS/3624/08
West-Call® Novus® Distribution Panel with 4x8 Audio Switch Matrix on 18x22 back panel. No Field Home Run (FHR) Modules. Distribution Panel requires a TC-1822/6 (30116034) Terminal Cabinet. EV-ASM/EXT1 option not available on this panel.	NOVUS/1822/00
West-Call® Novus® Distribution Panel with 4x8 Audio Switch Matrix on 18x22 back panel. 1 Field Home Run (FHR) Modules. Each Field Home Run Module supports up to 16 patient rooms. A 28V power supply is required for each FHR. Distribution Panel requires a TC-1822/6 (30116034) Terminal Cabinet. EV-ASM/EXT1 option not available on this panel.	NOVUS/1822/01
West-Call® Novus® Distribution Panel with 4x8 Audio Switch Matrix on 18x22 back panel. 2 Field Home Run (FHR) Modules. Each Field Home Run Module supports up to 16 patient rooms. A 28V power supply is required for each FHR. Distribution Panel requires a TC-1822/6 (30116034) Terminal Cabinet. EV-ASM/EXT1 option not available on this panel.	NOVUS/1822/02
West-Call® Novus® Distribution Panel with 4x8 Audio Switch Matrix on 18x22 back panel. 3 Field Home Run (FHR) Modules. Each Field Home Run Module supports up to 16 patient rooms. A 28V power supply is required for each FHR. Distribution Panel requires a TC-1822/6 (30116034) Terminal Cabinet. EV-ASM/EXT1 option not available on this panel.	NOVUS/1822/03

Optional Equipment

Field Home Run Module. Remote panel supports 16 rooms. Includes required electronics, PS-28 and 12-12 Hoffman Box.	FHR Module
i-Dome® Home Run Module. Supports 64 i-Domes. Includes required electronics, PS-12 and 12x12 Hoffman Box.	i-Dome® HR Module
Adds an additional 4 masters and 8 audio paths when added to a Novus® Distribution Panel.	EV-ASM/EXP1
External Audio Interface. Used for phone interfaces or other external audio interfaces. Add to a Novus/3624/xx only.	EV-ASM/EXT1

Technical Specification

Operating Voltage	120 VAC and 12 VDC +/-10%
Power Consumption	80 watts
Size	32"H x 20"W x 5"D / 19 7/8"x17Wx5"D
Weight	Up to 15 pounds
Mounting Cabinet	36"H x 24"W x 6"D/22"Hx18Hx6"D
Cabinet Door	36"H x 24"W Flush mount louvered door order TCD-3624/F/LV Surface mount louvered door order TCD-3624/S/LV
Termination	CE100F22-8 Panduit connectors for master audio connections and CE156F22-3 for power connections. RJ-45 plugs for homerun data cables, master network cables, CNTR-1 network connections.
Audio Amplifier	True duplex (2 channel) amplifier with 30db gain and power output of 2 watts. One amplifier per audio channel, up to 16 channels.



View West-Com's complete West-Call® line of healthcare communications solutions at www.westcall.com

West-Com Nurse Call Systems, Inc.
2200 Cordelia Road • Fairfield, CA 94534 • 800-761-1180 • info@westcall.com